

## Reference Chart Recommended Seal for Each Device/Container

Description	Recommended Seal
AccuVote Optical Scan Tabulator	Easy Twist
M100 Optical Scan Tabulator	Easy Twist, Padlock
Optech Insight Optical Scan Tabulator	Easy Twist, Memory Pack
Metal Container (top load)	Pull-Tite, Flat Metal w/ Horseshoe
Metal Container (dual door/seal)	Pull-Tite
Plastic Bin 27"x17"x12.5"	Pull-Tite
Collapsible Ballot Storage Bag 14"x19"x14"	Pull-Tite
Election Security Chamber Bag 14"x19"x14"	Chamber
Election Security Chamber Bag w/Wheels 14"x19"x14"	Chamber
Election Security Chamber Bag 10"x19"x12"	Chamber
Light Duty Courier Chamber Bag 16"x22"x6"	Chamber
Light Duty Courier Chamber Bag 14"x18"x4"	Chamber
Ballot Transfer Flat Bag 12"x19"x10"	Chamber
Duffle Bag 12"x19"x10"	Pull-Tite
Titan Security Bag 22"x6"x16"	Pull-Tite
Election Security Chamber Bag 19"x13"	Chamber
Election Security Chamber Bag 16" x 13"	Chamber
Expandable Provisional Ballot Chamber Bag 6"x13"x2"	Chamber
Provisional Ballot Chamber Bag 22"x19"	Chamber
Provisional Ballot Security Bag 18" x 14"	Pull-Tite
Handi – Pouch Security Bag 18"x14"	Pull-Tite
Election Security Chamber Bag 9"x11"	Chamber
Single Module Transport Chamber Bag 8" x 10"	Chamber
Data Module Transport Chamber Bag 10"x12"	Chamber
Memory Pouch 7"x8.5"	Padlock

### For More Information

Properly Sealing Containers with Applicable Seals:

[http://www.michigan.gov/sos/0,1607,7-127-1633\\_11976-251495--,00.html](http://www.michigan.gov/sos/0,1607,7-127-1633_11976-251495--,00.html)

Sealing Ballot Containers Training Videos:

<http://www.youtube.com/playlist?list=PLJHaXzzP47I8zVfIDEwPAkT4bKvtUYaj>

Approved Ballot Containers with Closure Type:

[http://www.michigan.gov/sos/0,1607,7-127-1633\\_11976-185731--,00.html](http://www.michigan.gov/sos/0,1607,7-127-1633_11976-185731--,00.html)

Transfer Containers with Closure Type:

[http://www.michigan.gov/sos/0,1607,7-127-1633\\_11976-185887--,00.html](http://www.michigan.gov/sos/0,1607,7-127-1633_11976-185887--,00.html)